




LTN NEURO SELECT 5-DL LTN-P NEURO SELECT 5-DL

LUTINA PHOTO
GY & BR & SB

Back-side progressive + Back-side aspheric design

※The lens may be a cataract lens depending on the power




Corridor	11,12,13,14,15mm
Addition	0.50D to 4.00D at 0.25 steps

Color Name	Category Number	Visible Transmittance (%)	Capability for Driving	Capability for Driving at Night
LUTINA Photochromic Brown	0/2	90/23	○	○
LUTINA Photochromic Gray	0/3	90/15	○	○
LUTINA Photochromic Surf Blue Only for INDEX 1.60	0/1	92/53	○	○

Option for MT, i, MTi		
MT	Mytune	Frame shape information required.
i	Individual	Individual parameters can be specified.
MTi	Mytune & Individual	Frame shape information required. Individual parameters can be specified.
Individual parameters	Wrap angle (Default value: 0.0°)	0.0° ~ 15.0° (0.1°steps)
	Tilt angle (Default value: 8.0°)	-5.0° ~ 25.0° (0.1°steps)
	Vertex distance (Default value: 12.0mm)	8.0mm ~ 25.0mm (0.1mm steps)
	Inset	0.0 to 5.0 mm at 0.1 mm steps
Inset	Inset design from other elements	Designed by far PD, power, reading distance, wrap angle, tilt angle and vertex distance
Reading distance	Reading distance can be prescribed	25cm to 80cm at 1cm steps

Design & Option	Corridor	Index
N	5	N 11mm
	5 (MT)	T 12mm
	5 (i)	S 13mm
	5 (MTi)	E 14mm
		R 15mm

Specifications	Specifiable range / Availability
Size reduction	by 50mm Min : only (+), 1mm step
Prism	Up to 3 prism
Decentration	Not available
Base curve selection	Available
Slice (Frame shape required)	Available for plus & mixed power lenses
Remote edging	Available
Fine edge processing	Available (Less S+C = -3.00 : Not available)



Design & Option	Corridor	Index
N	5	N 11mm
	5 (MT)	T 12mm
	5 (i)	S 13mm
	5 (MTi)	E 14mm
		R 15mm

Lens mark	
A	Fitting point (far vision eye point)
B	Area to measure the far vision power
C	Geometrical center
D	Area to measure the near vision power
E	Addition
F	Inset (0.0 to 5.0 mm at 0.1 mm steps)
G	Identification and location mark