




※The lens may be a cataract lens depending on the power




Corridor	21,22,23mm
Addition	1.00D to 3.50D at 0.25 steps
Design type	Mild, Clear, New Balance, Wide

Color Name	Category Number	Visible Transmittance (%)	Capability for Driving	Capability for Driving at Night
LUTINA Photochromic Brown	0/2	90/23	○	○
LUTINA Photochromic Gray	0/3	90/15	○	○

Frame shape information must be required.	
Individual parameters	Wrap angle (Default value: 0.0°) 0.0° ~ 15.0° (0.1°steps)
	Tilt angle (Default value: 8.0°) -5.0° ~ 25.0° (0.1°steps)
	Vertex distance (Default value: 12.0mm) 8.0mm ~ 25.0mm (0.1mm steps)

Inset	Inset	0.0 to 5.0 mm at 0.1 mm steps
	Inset design from other elements	Designed by far PD, power, reading distance, wrap angle, tilt angle and vertex distance
Reading distance	Reading distance can be prescribed	25cm to 80cm at 1cm steps

Specifications	Specifiable range / Availability
Size reduction	by 50mm Min : only (+), 1mm step
Prism	Up to 3 prism
Decentration	Not available
Base curve selection	Available
Slice (Frame shape required)	Available for plus & mixed power lenses
Remote edging	Available
Fine edge processing	Available (Less S+C = -3.00 : Not available)



Design type	Corridor	Index	Design type
W Wide	L 21mm	Z 1.76	M Mild
L Long	I 22mm	U 1.67	C Clear
	H 23mm	B 1.60	N New Balance
			W Wide

Lens mark	
A	Fitting point (far vision eye point)
B	Area to measure the far vision power
C	Geometrical center
D	Area to measure the near vision power
E	Addition
F	Inset (0.0 to 5.0 mm at 0.1 mm steps)
G	Identification and location mark